

# SLEEVE TYPE FLEXIBLE COUPLINGS




## > MATERIAL:

- Sleeve - Polyethylene
- Insert - Acetal
- Hubs - Aluminum Alloy, Anodized

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

## > SPECIFICATIONS:


	Series	
	21	23
Max. hp @ 1750 rpm	1/20	1/2
Max. Angular Offset	3°	7°
Max. Lateral Offset	.005	.015
Max. Torque lbf in.	.6	18



## > BUILD YOUR OWN COUPLING:

**For Different Bore Combinations:** Select insert and hub assemblies and corresponding sleeve within the same series.

**For Hubs with the Same Bore:** Select the "Complete Coupling"



## INCH COMPONENT

Catalog Number			O.D.	B Bore +.001 -.000	L Length	E Sleeve Length	C Hub Dia.	D Hub Length	Set Screw
Complete Coupling	Insert & Hub Assembly	Sleeve Only							
A 5Z21-1604	A 5T21-1604	A 5R21-16	37/64	.125	15/16	7/16	9/16	7/32	#4-40
A 5Z21-1606	A 5T21-1606			.1875					#6-32
A 5Z21-1608	A 5T21-1608			.250					
A 5Z23-3210	A 5T23-3210	A 5R23-32	1-5/64	.3125	1-9/16	11/16	1	3/8	#8-32
A 5Z23-3212	A 5T23-3212			.375					#10-32
A 5Z23-3214	A 5T23-3214			.4375					
A 5Z23-3216	A 5T23-3216			.500					1/4-20

Sleeve Stock Catalog Number	O.D.	Length Inch
A 5R21-16S	1/2	10
A 5R23-32S	1	12



6-68  
D820

REV:  
4/27/23

