

MOLDED UNIVERSAL JOINTS



WITH MOLDED SLIDE EXTENSION
ECONOMY SERIES

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



> MATERIAL:

Body & Spider - Molded Acetal

> MAX. OPERATING TEMPERATURE:

180°F

> SPECIFICATIONS:

Max. Angular Displacement: 90°

*Max. Recommended Extension: 3/4




Fig. 1




Fig. 2

INCH COMPONENT

Catalog Number	B Bore +.000 -.002	Bore Depth (Typ)	Max. Recommended Torque lbf in.	
			Closed	Open*
Fig. 1				
A 5M 8-SE306	3/16	.34	6	5
A 5M 8-SE308	1/4			
Fig. 2				
A 5M 8-SE406	3/16	.42	12	10
A 5M 8-SE408	1/4			
A 5M 8-SE410	5/16			

7-15
D820

REVISED:
05/19/23

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16