

# MOLDED UNIVERSAL JOINTS • TELESCOPING



WITH MOLDED SLIDE EXTENSION  
ECONOMY SERIES

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



**> MATERIAL:**

Body & Spider - Molded Acetal

**> MAX. OPERATING TEMPERATURE:**

+85°C

**> SPECIFICATIONS:**

Max. Angular Displacement: 90°

\*Max. Recommended Extension: 19 mm




Fig. 1




Fig. 2

**METRIC COMPONENT**

| Catalog Number | d<br>Bore<br>0<br>-0.05 | Bore<br>Depth<br>(Typ) | Max. Recommended Torque<br>N • m |       |
|----------------|-------------------------|------------------------|----------------------------------|-------|
|                |                         |                        | Closed                           | Open* |
| <b>Fig. 1</b>  |                         |                        |                                  |       |
| A 5M 8MSE304   | 4                       | 8.6                    | 0.7                              | 0.5   |
| A 5M 8MSE306   | 6                       |                        |                                  |       |
| <b>Fig. 2</b>  |                         |                        |                                  |       |
| A 5M 8MSE406   | 6                       | 10.6                   | 1.4                              | 1.1   |
| A 5M 8MSE408   | 8                       |                        |                                  |       |

