

GROOVELESS RETAINING RINGS

SDP/SI

EXTERNAL
FOR AXIAL ASSEMBLY
NO GROOVE REQUIRED

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM




› MATERIAL / FINISH:

Spring Steel HRC 46...52, Black Oxide Finish

› SPECIFICATION:

- Shaft Tolerance (h9): 2 to 3 mm 0/-0.025
- (h11): 4 to 6 mm 0/-0.075
- (h11): 7 to 10 mm 0/-0.090
- (h11): 12 & 16 mm 0/-0.110
- (h11): 20 mm 0/-0.130

Priced Per Each



METRIC COMPONENT

Catalog Number	D Shaft Dia.	D ₁ Ring Clearance	H Ring Height	Thickness		Allowable Axial Load N
				S	Tol.	
S73NW2MGR555-020	2	5.8	5.2	0.5	± 0.03	50
S73NW2MGR555-025	2.5	6.5	5.9	0.6		60
S73NW2MGR555-030	3	7.4	6.8	0.7		75
S73NW2MGR555-040	4	9	8.3	0.8		100
S73NW2MGR555-050	5	10.2	9.75			130
S73NW2MGR555-060	6	11.4	11.1	1	± 0.04	170
S73NW2MGR555-070	7	12.8	12.5			180
S73NW2MGR555-080	8	14.8	14.3			200
S73NW2MGR555-100	10	17.5	16.9	1.2	± 0.05	250
S73NW2MGR555-120	12	21	20.6			300
S73NW2MGR555-160	16	28.5	26.5	1.5	± 0.05	500
S73NW2MGR555-200	20	35	33.25			750

