

# COMMERCIAL BALANCED-TYPE SHAFT/HUB CLAMPS

# SDPSI

REDUCED CLEARANCE RADIUS

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

**> MATERIAL:**

Carbon Steel  
303 Stainless Steel


**> SPECIFICATIONS:**

Tolerances	
Decimals	± .010
Fractions	± 1/32

Stainless Steel socket head cap screw supplied.



SDPSI • SDPSI



## INCH COMPONENT

Catalog Number	Shaft Size	I.D.* +.002 -.000	H	T	W	Screw Size	R
<b>Carbon Steel</b>							
S3301Y-J103	1/8	.188	11/16	.140	.312	#2-56	25/64
S3301Y-J104	3/16	.251	51/64		.375		15/32
S3301Y-J105	1/4	.313	13/16		.437		31/64
S3301Y-J106	5/16	.376	7/8		.500		17/32
S3301Y-J107	3/8	.438	1-1/32		.625		39/64
S3301Y-J093	1/8	.188	11/16	.250	.312	#6-32	25/64
S3301Y-J094	3/16	.251	51/64		.375		15/32
S3301Y-J095	1/4	.313	13/16		.437		31/64
S3301Y-J096	5/16	.376	7/8		.500		17/32
S3301Y-J097	3/8	.438	1-1/32		.625		39/64
<b>303 Stainless Steel</b>							
S3301Y-J093S	1/8	.188	11/16	.250	.312	#6-32	25/64
S3301Y-J094S	3/16	.251	51/64		.375		15/32
S3301Y-J095S	1/4	.313	13/16		.437		31/64
S3301Y-J096S	5/16	.376	7/8		.500		17/32
S3301Y-J097S	3/8	.438	1-1/32		.625		39/64

\* Dimensions apply before slot is made.

4-37  
D-820

REVISED:  
6/21/23

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16