

# L TIMING BELTS • 3/8" OR 9.525 mm PITCH



## BELT WIDTHS

INCH - 1/2, 3/4 & 1 in.

METRIC - 12.5, 19 & 25.4 mm

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



## > MATERIAL:

Neoprene - Nylon Covered, Fiberglass Reinforced

## > SPECIFICATIONS:

### Breaking Strength:

125 lbf per 1/8 in. (175 N per 1 mm) Belt Width; not representative of the load-carrying capacity of the belt.

### Temperature Range:


-30°F to +185°F (-34°C to +85°C)



## > MODIFICATIONS:

Special Widths - cut to size from sleeves available from stock.

Pulleys are available with inch or metric standards.



NOTE: Dimensions in ( ) are mm.

## INCH COMPONENT CATALOG NUMBER

A 6 R 4 -

No. of Grooves Code

Belt Width Inch	Width Code
1/2	050
3/4	075
1	100

## METRIC COMPONENT CATALOG NUMBER

A 6 R 4 M

No. of Grooves Code

Belt Width mm	Width Code
12.5	125
19	190
25.4	254

Groove Code	Pitch Length	
	Inch	mm
026	9.750	247.65
029	10.875	276.23
033	12.375	314.33
035	13.125	333.38
036	13.500	342.9
038	14.250	361.95
040	15.000	381
041	15.375	390.53
042	15.750	400.05
044	16.500	419.1
045	16.875	428.63
046	17.250	438.15
047	17.625	447.68
050	18.750	476.25
052	19.500	495.3
053	19.875	504.83
054	20.250	514.35
055	20.625	523.88
056	21.000	533.4
058	21.750	552.45
060	22.500	571.5
062	23.250	590.55
063	23.625	600.08
064	24.000	609.6
065	24.375	619.13
066	24.750	628.65
067	25.125	638.18
068	25.500	647.7

Groove Code	Pitch Length	
	Inch	mm
069	25.875	657.23
070	26.250	666.75
072	27.000	685.8
074	27.750	704.85
076	28.500	723.9
080	30.000	762
081	30.375	771.53
082	30.750	781.05
084	31.500	800.1
085	31.875	809.63
086	32.250	819.15
089	33.375	847.73
090	33.750	857.25
092	34.500	876.3
094	35.250	895.35
096	36.000	914.4
098	36.750	933.45
100	37.500	952.5
104	39.000	990.6
105	39.375	1000.13
108	40.500	1028.7
112	42.000	1066.8
114	42.750	1085.85
116	43.500	1104.9
117	43.875	1114.43
119	44.625	1133.48
120	45.000	1143
123	46.125	1171.58

Continued on the next page



**INCH COMPONENT CATALOG NUMBER**

A 6 R 4 -

No. of Grooves Code

Belt Width Inch	Width Code
1/2	050
3/4	075
1	100

**METRIC COMPONENT CATALOG NUMBER**

A 6 R 4 M

No. of Grooves Code

Belt Width mm	Width Code
12.5	125
19	190
25.4	254

Groove Code	Pitch Length	
	Inch	mm
124	46.500	1181.1
128	48.000	1219.2
136	51.000	1295.4
140	52.500	1333.5
144	54.000	1371.6
146	54.750	1390.65
151	56.625	1438.28
152	57.000	1447.8
154	57.750	1466.85
155	58.125	1476.38
160	60.000	1524
161	60.375	1533.53
165	61.875	1571.63
168	63.000	1600.2
174	65.250	1657.35
176	66.000	1676.4
186	69.750	1771.65
192	72.000	1828.8
194	72.750	1847.85
195	73.125	1857.38
208	78.000	1981.2
210	78.750	2000.25
215	80.625	2047.88
218	81.750	2076.45
228	85.500	2171.7
230	86.250	2190.75
235	88.125	2238.38
240	90.000	2286

Groove Code	Pitch Length	
	Inch	mm
244	91.500	2324.1
250	93.750	2381.25
252	94.500	2400.3
294	110.250	2800.35
340	127.500	3238.5

Continued from the previous page

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16