


FOR NO. 25 SINGLE STRAND CHAINS  
.110 FACE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



**> MATERIAL:**  
Steel

These sprockets can be used with #25,  
1/4" pitch roller or ladder chains.



**INCH COMPONENT**

Catalog Number	No. of Teeth	P.D.	O.D. (Ref.)	B Bore	E Length	C Hub	D Hub Proj.	S	Set Screw
A 6C 7-25B09	9	.731	.84	1/4	1/2	7/16	25/64	3/16	#10-32
A 6C 7-25B10	10	.809	.92	1/4	1/2	1/2	25/64	3/16	#10-32
A 6C 7-25B11	11	.887	1.00	1/4	1/2	9/16	25/64	3/16	#10-32
A 6C 7-25B12	12	.966	1.08	1/4	1/2	5/8	25/64	3/16	#10-32
A 6C 7-25B13	13	1.045	1.16	1/4	1/2	23/32	25/64	3/16	#10-32
A 6C 7-25B14	14	1.124	1.25	1/4	1/2	13/16	25/64	3/16	#10-32
A 6C 7-25B15	15	1.203	1.33	1/4	1/2	7/8	25/64	3/16	#10-32
A 6C 7-25B16	16	1.282	1.41	1/4	1/2	31/32	25/64	3/16	#10-32
A 6C 7-25B17	17	1.361	1.49	1/4	1/2	1-1/32	25/64	3/16	#10-32
A 6C 7-25B18	18	1.440	1.57	1/4	1/2	1-1/8	25/64	3/16	#10-32
A 6C 7-25B19	19	1.519	1.65	1/4	1/2	1-7/32	25/64	3/16	#10-32
A 6C 7-25B20	20	1.598	1.73	1/4	5/8	1-9/32	33/64	3/16	#10-32
A 6C 7-25B21	21	1.678	1.81	1/4	5/8	1-3/8	33/64	3/16	#10-32
A 6C 7-25B22	22	1.757	1.89	1/4	5/8	1-7/16	33/64	3/16	#10-32
A 6C 7-25B23	23	1.836	1.97	1/4	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B24	24	1.915	2.05	3/8	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B25	25	1.995	2.13	3/8	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B26	26	2.074	2.21	3/8	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B28	28	2.233	2.37	3/8	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B30	30	2.392	2.53	3/8	5/8	1-1/2	33/64	3/16	#10-32
A 6C 7-25B31	31	2.471	2.61	3/8	5/8	1-1/2	33/64	1/4	1/4-20
A 6C 7-25B32	32	2.551	2.69	3/8	5/8	1-1/2	33/64	1/4	1/4-20
A 6C 7-25B36	36	2.869	3.01	3/8	5/8	1-1/2	33/64	1/4	1/4-20
A 6C 7-25B40	40	3.187	3.33	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B45	45	3.584	3.73	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B48	48	3.823	3.96	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B54	54	4.300	4.44	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B60	60	4.777	4.92	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B70	70	5.572	5.72	1/2	3/4	2	41/64	1/4	1/4-20
A 6C 7-25B72	72	5.732	5.88	1/2	3/4	2	41/64	1/4	1/4-20

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16