


FLAT HEAD
FILLISTER HEAD
ROUND HEAD

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:
18-8 Stainless Steel

> SPECIFICATION:
Priced Per 100 Pieces

* Length of flat head screws include head height.



INCH COMPONENT

Catalog Number			Thread Size	L Length
Flat Head	Fillister Head	Round Head		
A 9X16-F008002	A 9X16-P008002	A 9X16-R008002	#0-80	1/8
A 9X16-F008003	A 9X16-P008003	A 9X16-R008003	#0-80	3/16
A 9X16-F008004	A 9X16-P008004	A 9X16-R008004	#0-80	1/4
A 9X16-F008005	A 9X16-P008005	A 9X16-R008005	#0-80	5/16
A 9X16-F008006	A 9X16-P008006	A 9X16-R008006	#0-80	3/8
A 9X16-F008008	A 9X16-P008008	A 9X16-R008008	#0-80	1/2
A 9X16-F025603	A 9X16-P025603	A 9X16-R025603	#2-56	3/16
A 9X16-F025604	A 9X16-P025604	A 9X16-R025604	#2-56	1/4
A 9X16-F025605	A 9X16-P025605	A 9X16-R025605	#2-56	5/16
A 9X16-F025606	A 9X16-P025606	A 9X16-R025606	#2-56	3/8
A 9X16-F025608	A 9X16-P025608	A 9X16-R025608	#2-56	1/2
A 9X16-F044003	A 9X16-P044003	A 9X16-R044003	#4-40	3/16
A 9X16-F044004	A 9X16-P044004	A 9X16-R044004	#4-40	1/4
A 9X16-F044005	A 9X16-P044005	A 9X16-R044005	#4-40	5/16
A 9X16-F044006	A 9X16-P044006	A 9X16-R044006	#4-40	3/8
A 9X16-F044008	A 9X16-P044008	A 9X16-R044008	#4-40	1/2
A 9X16-F044010	A 9X16-P044010	A 9X16-R044010	#4-40	5/8
A 9X16-F063203	A 9X16-P063203	A 9X16-R063203	#6-32	3/16
A 9X16-F063204	A 9X16-P063204	A 9X16-R063204	#6-32	1/4
A 9X16-F063205	A 9X16-P063205	A 9X16-R063205	#6-32	5/16
A 9X16-F063206	A 9X16-P063206	A 9X16-R063206	#6-32	3/8
A 9X16-F063208	—	A 9X16-R063208	#6-32	1/2
A 9X16-F063210	A 9X16-P063210	A 9X16-R063210	#6-32	5/8
A 9X16-F063212	A 9X16-P063212	A 9X16-R063212	#6-32	3/4
A 9X16-F083204	A 9X16-P083204	A 9X16-R083204	#8-32	1/4
A 9X16-F083205	—	—	#8-32	5/16
A 9X16-F083206	A 9X16-P083206	—	#8-32	3/8
—	A 9X16-P083208	A 9X16-R083208	#8-32	1/2
A 9X16-F083210	A 9X16-P083210	A 9X16-R083210	#8-32	5/8
—	A 9X16-P083212	A 9X16-R083212	#8-32	3/4
A 9X16-F083216	—	A 9X16-R083216	#8-32	1
A 9X16-F103204	A 9X16-P103204	A 9X16-R103204	#10-32	1/4
—	A 9X16-P103205	A 9X16-R103205	#10-32	5/16
—	—	A 9X16-R103206	#10-32	3/8
A 9X16-F103208	A 9X16-P103208	A 9X16-R103208	#10-32	1/2
—	A 9X16-P103210	A 9X16-R103210	#10-32	5/8
A 9X16-F103212	—	A 9X16-R103212	#10-32	3/4
A 9X16-F103216	A 9X16-P103216	A 9X16-R103216	#10-32	1
A 9X16-F252004	A 9X16-P252004	—	1/4-20	1/4
—	A 9X16-P252005	—	1/4-20	5/16
A 9X16-F252006	A 9X16-P252006	A 9X16-R252006	1/4-20	3/8
A 9X16-F252008	A 9X16-P252008	—	1/4-20	1/2
A 9X16-F252010	A 9X16-P252010	—	1/4-20	5/8
A 9X16-F252012	A 9X16-P252012	A 9X16-R252012	1/4-20	3/4
A 9X16-F252016	A 9X16-P252016	A 9X16-R252016	1/4-20	1

I
R
T
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16