

HEXAGONAL STAND-OFFS




THREADED
SWAGE TYPE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

303 Stainless Steel



INCH COMPONENT

Catalog Number	H Height	L Length	Panel Thickness
*S5921Y-SO10-01	1/8	.075	1/32
S5921Y-SO10-05	3/16	.075	1/32
S5921Y-SO10-09	1/4	.075	1/32
S5921Y-SO10-17	3/8	.075	1/32
S5921Y-SO10-25	1/2	.075	1/32
*S5921Y-SO10-02	1/8	.105	1/16
S5921Y-SO10-02A	1/8	.105	1/16
S5921Y-SO10-06	3/16	.105	1/16
S5921Y-SO10-10	1/4	.105	1/16
S5921Y-SO10-18	3/8	.105	1/16
S5921Y-SO10-26	1/2	.105	1/16
S5921Y-SO10-03A	1/8	.135	3/32
S5921Y-SO10-07	3/16	.135	3/32
S5921Y-SO10-11	1/4	.135	3/32
S5921Y-SO10-19	3/8	.135	3/32
S5921Y-SO10-27	1/2	.135	3/32
S5921Y-SO10-04A	1/8	.165	1/8
S5921Y-SO10-08	3/16	.165	1/8
S5921Y-SO10-12	1/4	.165	1/8
S5921Y-SO10-20	3/8	.165	1/8
S5921Y-SO10-28	1/2	.165	1/8
S5921Y-SO10-29	1/8	.230	3/16
S5921Y-SO10-30	3/16	.230	3/16
S5921Y-SO10-31	1/4	.230	3/16
S5921Y-SO10-32	3/8	.230	3/16
S5921Y-SO10-33	1/2	.230	3/16

* Items with #4-40 thread.

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10**
- 11
- 12
- 13
- 14
- 15
- 16