

PRECISION SCREW-TYPE SHAFT/HUB CLAMPS



MINIATURE FOR 1/16 SHAFT

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



> MATERIAL:

303 Stainless Steel

> SPECIFICATIONS:

Tolerances	
Decimals	± .005

Recommended for use with S9490A-T700 Differential.
Four Stainless Steel socket head set screws supplied.



INCH COMPONENT

Catalog Number	I.D. +.001 -.000	A Dia.	Screw Size
S3600Y-C131	.0995	.312	#2-56

STANDARD



> MATERIAL:

303 Stainless Steel
2024-T351 Aluminum, Anodized

> SPECIFICATIONS:

Tolerances	
Decimals	± .005

Four Stainless Steel socket head set screws supplied.



INCH COMPONENT

Catalog Number		I.D. +.001 -.000	A Dia.	Screw Size
303 Stainless Steel	2024-T351 Aluminum Anodized			
S3600Y-C123	S3600Y-C127	.1255	.375	#4-40
S3600Y-C124	S3600Y-C128	.1880		
S3600Y-C125	S3600Y-C129	.2505		
S3600Y-C126	S3600Y-C130	.3130	.500	#6-32

4-52
D820

REVISED:
6/26/23

1

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

COMMERCIAL SCREW-TYPE SHAFT/HUB CLAMPS



MINIATURE FOR 1/16 SHAFT

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM



> MATERIAL:

303 Stainless Steel

> SPECIFICATIONS:

Tolerances	
Decimals	± .010

Four Stainless Steel socket head set screws supplied.



INCH COMPONENT

Catalog Number	I.D. +.002 -.000	A Dia.	B	Screw Size
S3600Y-J131	.0995	.312	.125	#2-56

STANDARD



> MATERIAL:

303 Stainless Steel
2024-T351 Aluminum

> SPECIFICATIONS:

Tolerances	
Decimals	± .010

Four Stainless Steel socket head set screws supplied.



INCH COMPONENT

Catalog Number		I.D. +.002 -.000	A Dia.	B	Screw Size
303 Stainless Steel	2024-T351 Aluminum				
S3600Y-J123	S3600Y-J127	.1255	.375	.250	#4-40
S3600Y-J124	S3600Y-J128	.1880			
S3600Y-J125	S3600Y-J129	.2505			
S3600Y-J126	S3600Y-J130	.3130	.500		#6-32

4-53
D820

REVISED:
6/26/23

I

R

T

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16