


**> MATERIAL:**

Acetal with PTFE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

**> TEMPERATURE RANGE:**

32° F to 180° F



**INCH COMPONENT**

Catalog Number	Screw Size	Number of Starts	Lead in.	Efficiency %	O.D.	L
AB21SN-25161	1/4-16	1	.063	48	.625	.500
AB21SN-25201	1/4-20		.050	41		
AB21SN-31082	5/16-8	2	.250	72	.750	.750
AB21SN-31084		4	.500	80		
AB21SN-31122	5/16-12	2	.167	65		
AB21SN-37081	3/8-8	stub	.125	53		
AB21SN-37084		4	.500	79		
AB21SN-37101	3/8-10	1	.100	49		
AB21SN-37102		2	.200	65		
AB21SN-37114	3/8-11	4	.375	75		
AB21SN-37121	3/8-12	1	.083	44		
AB21SN-37122		2	.167	60		
AB21SN-37161	3/8-16	1	.063	36		

Catalog Number (Ref.)	C	TH	Design Load lbf	Max. Static Load lbf	Use with Flange
AB21SN-25161	.187	9/16-18	45	225	AB250F-025
AB21SN-25201					AB250F-025
AB21SN-31082	.250	5/8-18	70	350	AB250F-037
AB21SN-31084					
AB21SN-31122					
AB21SN-37081					
AB21SN-37084					
AB21SN-37101					
AB21SN-37102					
AB21SN-37114					
AB21SN-37121					
AB21SN-37122					
AB21SN-37161					


Continued on the next page

I  
R  
T  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16

**> MATERIAL:**  
Acetal with PTFE

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

**> TEMPERATURE RANGE:**  
32° F to 180° F



**INCH COMPONENT**

Catalog Number	Screw Size	Number of Starts	Lead in.	Efficiency %	O.D.	L	
AB21SN-43082	7/16-8	2	.250	65	1.000	1.000	
AB21SN-43084		4	.500	76			
AB21SN-50042	1/2-4	2		75			
AB21SN-50101	1/2-10	1	.100	41			
AB21SN-50102		2	.200	57			
AB21SN-62101	5/8-10	1	.100	35			
AB21SN-62102		2	.200	51			
AB21SN-75061	3/4-6	1	.167	44			1.500
AB21SN-75081	3/4-8		.125	36			
AB21SN-75101	3/4-10		.100	31			
AB21SN-10008	1-8		.125	29			
AB21SN-10010	1-10			.100	25		

Catalog Number (Ref.)	C	TH	Design Load lbf	Max. Static Load lbf	Use with Flange		
AB21SN-43082	.375	15/16-16	100	500	AB250F-050		
AB21SN-43084							
AB21SN-50042			150	750			
AB21SN-50101							
AB21SN-50102						160	800
AB21SN-62101							
AB21SN-62102	.500	1-3/8-16	300	1500	AB250F-075		
AB21SN-75061							
AB21SN-75081			400	2000			
AB21SN-75101							
AB21SN-10008							
AB21SN-10010							

Continued from the previous page

