

PRECISION DOWEL PINS





> MATERIAL:

300 Series Stainless Steel, Clear Passivated

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

Priced Per 100 Pieces

Other lengths and diameters available on special order.



* Chamfer or round ends at SDP option.

INCH COMPONENT

Catalog Number	D Dia. +.0002 -.0000	L Length ± .010
A 9X31-0103	.0312	.094
A 9X31-0104		.125
A 9X31-0105		.156
A 9X31-0106		.188
A 9X31-0107		.219
A 9X31-0108		.250
A 9X31-0110		.312
A 9X31-0112		.375
A 9X31-0114		.438
A 9X31-0116		.500
A 9X31-0118		.562
A 9X31-0120		.625
A 9X31-0124		.750
A 9X31-0128		.875
A 9X31-0203	.0625	.094
A 9X31-0204		.125
A 9X31-0205		.156
A 9X31-0206		.188
A 9X31-0207		.219
A 9X31-0208		.250
A 9X31-0210		.312
A 9X31-0212		.375
A 9X31-0214		.438
A 9X31-0216		.500
A 9X31-0218		.562
A 9X31-0220		.625
A 9X31-0224		.750
A 9X31-0228		.875
A 9X31-0232	1.000	
A 9X31-0303	.0937	.094
A 9X31-0304		.125
A 9X31-0305		.156
A 9X31-0306		.188
A 9X31-0307		.219
A 9X31-0308		.250
A 9X31-0310		.312
A 9X31-0312		.375
A 9X31-0314		.438
A 9X31-0316		.500
A 9X31-0318		.562
A 9X31-0320		.625
A 9X31-0324		.750
A 9X31-0328		.875
A 9X31-0332	1.000	
A 9X31-0340	1.250	

Catalog Number	D Dia. +.0002 -.0000	L Length ± .010
A 9X31-0344	.0937	1.375
A 9X31-0348		1.500
A 9X31-0403		.094
A 9X31-0404		.125
A 9X31-0405		.156
A 9X31-0406		.188
A 9X31-0407		.219
A 9X31-0408		.250
A 9X31-0410		.312
A 9X31-0412		.375
A 9X31-0414	.1250	.438
A 9X31-0416		.500
A 9X31-0418		.562
A 9X31-0420		.625
A 9X31-0424		.750
A 9X31-0428		.875
A 9X31-0432		1.000
A 9X31-0440		1.250
A 9X31-0444		1.375
A 9X31-0448		1.500
A 9X31-0456	.1875	1.750
A 9X31-0464		2.000
A 9X31-0608		.250
A 9X31-0610		.312
A 9X31-0612		.375
A 9X31-0614		.438
A 9X31-0616		.500
A 9X31-0620		.625
A 9X31-0624		.750
A 9X31-0628		.875
A 9X31-0632	.2500	1.000
A 9X31-0640		1.250
A 9X31-0648		1.500
A 9X31-0656		1.750
A 9X31-0664		2.000
A 9X31-0816		.500
A 9X31-0820		.625
A 9X31-0824		.750
A 9X31-0828		.875
A 9X31-0832		1.000
A 9X31-0840	1.250	
A 9X31-0848	1.500	
A 9X31-0856	1.750	
A 9X31-0864	2.000	

