

STAINLESS STEEL SPIROL PINS



STANDARD DUTY


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

300 Stainless Steel

> SPECIFICATION:

Priced Per 100 Pieces



INCH COMPONENT

Catalog Number	O.D.	O.D. Tolerance	L Length ± .01	Drill Size	Drill Size Tolerance
Shaft Size 3/32					
S7220Y-03304	.033	+.002/- .000	1/8	.031	+.001/- .000
S7220Y-03306			3/16		
S7220Y-03308			1/4		
S7220Y-03310			5/16		
S7220Y-03312			3/8		
Shaft Size 1/8					
S7220Y-04106	.041	+.003/- .000	3/16	.039	+.001/- .000
S7220Y-04108			1/4		
S7220Y-04110			5/16		
S7220Y-04112			3/8		
S7220Y-04114			7/16		
S7220Y-04116	1/2				
S7220Y-04906	.049	+.003/- .000	3/16	.047	± .001
S7220Y-04908			1/4		
S7220Y-04910			5/16		
S7220Y-04912			3/8		
S7220Y-04914			7/16		
S7220Y-04916	1/2				
S7220Y-05406	.054	+.003/- .000	3/16	.052	± .001
S7220Y-05408			1/4		
S7220Y-05410			5/16		
S7220Y-05412			3/8		
S7220Y-05414			7/16		
S7220Y-05416	1/2				
Shaft Size 3/16					
S7220Y-06708	.067	+.005/- .000	1/4	.062	+.003/- .001
S7220Y-06710			5/16		
S7220Y-06712			3/8		
S7220Y-06714			7/16		
S7220Y-06716			1/2		
S7220Y-06718			9/16		
S7220Y-06720			5/8		
Shaft Size 1/4 & 5/16					
S7220Y-09912	.099	+.006/- .000	3/8	.094	+.003/- .001
S7220Y-09914			7/16		
S7220Y-09916			1/2		
S7220Y-09918			9/16		
S7220Y-09920			5/8		
S7220Y-09922	11/16				
Shaft Size 3/8, 7/16 & 1/2					
S7220Y-13112	.131	+.007/- .000	3/8	.125	+.004/- .001
S7220Y-13114			7/16		
S7220Y-13116			1/2		
S7220Y-13118			9/16		
S7220Y-13120			5/8		
S7220Y-13122			11/16		
S7220Y-13124			3/4		
S7220Y-13128			7/8		
S7220Y-13132			1		

