

OPEN SERIES
SELF-ALIGNING
LOW COST

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM





> MATERIAL:

Body - Anodized Aluminum
Bearing - Frelon® Lined Aluminum

> SPECIFICATIONS:

Bore Tolerance for **PRECISION** (F8):
12 & 16 mm +0.043/+0.016
20, 25 & 30 mm +0.053/+0.020

Bore Tolerance for **STANDARD**:
12 & 16 mm +0.093/+0.066
20, 25 & 30 mm +0.129/+0.096




The projections shown are per ISO convention.

CATALOG NUMBER DESIGNATION

S 6 1 P □ Z M □ □ F □ □ □

— P Precision
— S Standard



METRIC COMPONENT

Catalog Number	d Nom. Bore Size	H ± 0.015	H ₁ Height	A Width	A ₁ ± 0.013	L Length	T	N ₂ ± 0.15
S61P□ZM12F039	12	18	28	43	21.5	39	M5	23
S61P□ZM16F043	16	22	35	53	26.5	43	M6	26
S61P□ZM20F054	20	25	42	60	30	54	M8	32
S61P□ZM25F067	25	30	51	78	39	67	M10	40
S61P□ZM30F079	30	35	60	87	43.5	79	M10	45

Catalog Number (Ref.)	N ₃ ± 0.15	N ₄	N ₅	S	S ₂	S ₃	a Degree	Max. Load Rating N	Ass'y Weight kg
S61P□ZM12F039	32	11	16.5	4	32	34	66°	3950	0.096
S61P□ZM16F043	40	13	21	4	35	42	68°	5930	0.162
S61P□ZM20F054	45	18	24	5	45	50	60°	9265	0.267
S61P□ZM25F067	60	22	29	6	20	64	60°	14935	0.536
S61P□ZM30F079	68	22	34	6	30	72	60°	21010	0.831