


# TIMING PULLEY STOCK • 40 D.P.



ALSO FOR 2.07 mm PITCH PULLEYS

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

► MATERIAL:  
Aluminum Alloy



## INCH COMPONENT

Catalog Number	No. of Grooves	P.D.	O.D. +.000 -.003	C Shank Dia.	E Shank Length	L Minimum Usable Length
A 6A 5-010LT	10	.260	.246	3/16 - 7/32 [5/16] <sup>Δ</sup>	1	2
A 6A 5-011LT	11	.286	.272			
A 6A 5-012LT	12	.312	.298	1/4 [3/8] Δ		3
A 6A 5-013LT	13	.338	.324	5/16 [7/16] Δ		
A 6A 5-014LT	14	.364	.350			
A 6A 5-015LT	15	.390	.376	3/8 [1/2] Δ		7/8
A 6A 5-016LT	16	.416	.402			
A 6A 5-017LT	17	.442	.428	3/8	4	
A 6A 5-018LT	18	.468	.454			
A 6A 5-019LT	19	.494	.480	1/2	1 [3/4] Δ	
A 6A 5-020LT	20	.520	.506			
A 6A 5-021LT	21	.546	.532			
A 6A 5-022LT	22	.572	.558			
A 6A 5-023LT	23	.598	.584			
A 6A 5-024LT	24	.624	.610			
A 6A 5-025LT	25	.650	.636			
A 6A 5-026LT	26	.676	.662			
A 6A 5-027LT	27	.702	.688			
A 6A 5-028LT	28	.728	.714			
A 6A 5-029LT	29	.754	.740			
A 6A 5-030LT	30	.780	.766			
A 6A 5-031LT	31	.806	.792			
A 6A 5-032LT	32	.832	.818			
A 6A 5-033LT	33	.858	.844			
A 6A 5-034LT	34	.884	.870			
A 6A 5-035LT	35	.910	.896			
A 6A 5-036LT	36	.936	.922			
A 6A 5-038LT	38	.988	.974			
A 6A 5-039LT	39	1.014	1.000			

Δ Dimensions in [ ] may be substituted at SDP option.

Continued on the next page

- I
- R
- T
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16


# TIMING PULLEY STOCK • 40 D.P.



ALSO FOR 2.07 mm PITCH PULLEYS

PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:  
Aluminum Alloy



## INCH COMPONENT

Catalog Number	No. of Grooves	P.D.	O.D. +.000 -.003	C Shank Dia.	L Minimum Usable Length
A 6A 5-040LT	40	1.040	1.026	1/2	7
A 6A 5-042LT	42	1.092	1.078		
A 6A 5-044LT	44	1.144	1.130		
A 6A 5-045LT	45	1.170	1.156		
A 6A 5-048LT	48	1.248	1.234		
A 6A 5-050LT	50	1.300	1.286		
A 6A 5-051LT	51	1.326	1.312		
A 6A 5-054LT	54	1.404	1.390		
A 6A 5-055LT	55	1.430	1.416		
A 6A 5-056LT	56	1.456	1.442		
A 6A 5-057LT	57	1.482	1.468		
A 6A 5-060LT	60	1.560	1.546		
A 6A 5-064LT	64	1.664	1.650		
A 6A 5-065LT	65	1.690	1.676		
A 6A 5-066LT	66	1.716	1.702		
A 6A 5-070LT	70	1.820	1.806		
A 6A 5-072LT	72	1.872	1.858		
A 6A 5-075LT	75	1.950	1.936		
A 6A 5-080LT	80	2.080	2.066		
A 6A 5-082LT	82	2.132	2.118		
A 6A 5-084LT	84	2.184	2.170		
A 6A 5-088LT	88	2.288	2.274		
A 6A 5-090LT	90	2.340	2.326		
A 6A 5-096LT	96	2.496	2.482		
A 6A 5-098LT	98	2.548	2.534		
A 6A 5-100LT	100	2.600	2.586		
A 6A 5-102LT	102	2.652	2.638		
A 6A 5-108LT	108	2.808	2.794		
A 6A 5-110LT	110	2.860	2.846		
A 6A 5-120LT	120	3.120	3.106		
A 6A 5-130LT	130	3.380	3.366		
A 6A 5-140LT	140	3.640	3.626		
A 6A 5-150LT	150	3.900	3.886		
				3/4	8

Δ Dimensions in [ ] may be substituted at SDP option.

Continued from the previous page



# MXL PULLEY FLANGES • .080" OR 2.03 mm & 40 D.P. PITCH

# SDPSI

### > MATERIAL:

Aluminum Alloy


PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

### > SPECIFICATION:

Priced Per 25 Pieces



SDPSI • SDPSI • SDPSI



## INCH COMPONENT

Catalog Number	Pulley Grooves Ref.	Inch		Metric		W Width ± .010 (± 0.25)	T Thickness
		I.D. ± .003	O.D. ± .016	I.D. ± 0.08	O.D. ± 0.4		
A 6A 5-010FA	10	.188	.425	4.77	10.8	.045 (1.14)	.025 (0.64)
A 6A 5-011FA	11	.214	.450	5.44	11.4		
A 6A 5-012FA	12	.218	.480	5.54	12.2		
A 6A 5-013FA	13	.244	.505	6.2	12.8		
A 6A 5-014FA	14	.270	.530	6.86	13.5		
A 6A 5-015FA	15	.296	.555	7.52	14.1		
A 6A 5-016FA	16	.322	.580	8.18	14.7		
A 6A 5-018FA	18	.374	.635	9.5	16.1		
A 6A 5-020FA	20	.426	.685	10.82	17.4	.052 (1.32)	.032 (0.81)
A 6A 5-021FA	21	.452	.710	11.48	18		
A 6A 5-022FA	22	.452	.740	11.48	18.8		
A 6A 5-024FA	24	.504	.790	12.8	20.1		
A 6A 5-025FA	25	.530	.815	13.46	20.7		
A 6A 5-026FA	26	.556	.840	14.12	21.3		
A 6A 5-028FA	28	.574	.895	14.58	22.7		
A 6A 5-030FA	30	.626	.945	15.9	24		
A 6A 5-032FA	32	.678	1.000	17.22	25.4		
A 6A 5-033FA	33	.704	1.025	17.88	26		
A 6A 5-034FA	34	.722	1.050	18.34	26.7		
A 6A 5-035FA	35	.748	1.080	19	27.4		
A 6A 5-036FA	36	.774	1.105	19.66	28.1		
A 6A 5-038FA	38	.826	1.155	20.98	29.3		
A 6A 5-040FA	40	.874	1.210	22.2	30.7	.060 (1.52)	.040 (1.02)
A 6A 5-042FA	42	.926	1.260	23.52	32		
A 6A 5-044FA	44	.978	1.315	24.84	33.4		
A 6A 5-045FA	45	1.044	1.340	26.52	34		
A 6A 5-048FA	48	1.058	1.420	26.87	36.1		
A 6A 5-050FA	50	1.110	1.470	28.19	37.3		
A 6A 5-054FA	54	1.200	1.575	30.48	40		
A 6A 5-060FA	60	1.356	1.730	34.44	43.9		

NOTE: Dimensions in ( ) are mm.

- I
- R
- T
- 1
- 2**
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16