


PATENTED
 SELF-LOCKING
 VIBRATION-RESISTANT
 NONMARRING OF SHAFT
 INSTALLED WITH STANDARD TOOLS
 REUSABLE




> MATERIAL:

416 Stainless Steel, Passivated

> SPECIFICATIONS:

Used as a locking device for rigidly mounting mechanical components onto a shaft. Due to its asymmetric thread geometry, a large radial clamping force is produced when the nut is tightened. It is a precision, dynamically balanced product suitable for high-speed applications. This simple two-piece keyless fastener can be installed within seconds, reducing assembly costs. Tightening the nut causes the slotted sleeve to contract, gripping the shaft and clamping the part to the sleeve at the same time. Keyways and screws are now obsolete; can be installed on shafts with existing keyways.




Special sizes available upon request.

Sold in Pairs

METRIC COMPONENT

Catalog Number	A Dia. +0.025 0	B Dia. 0 -0.025	C	D	E	L
A 7Z36M0612	6	10	14	4	7	12
A 7Z36M1016	10	14	18	4	12	16
A 7Z36M1218	12	16	24	5	14	18

Diameters A and B concentric within 0.013 T.I.R.



A superior method for building frames, mounting shafts, pins, rails or any cylindrical components to thin sheet metal or plastic walls.



Ideal in slots or oversized holes used for shaft position or belt tension adjustment applications.



Mounts hubless gears, sprockets, pulleys, cams or any thin walled components onto a shaft. Offers infinite radial and axial adjustments and quick lock and release action.

