


Super Ball Bushing™ Pillow Blocks (Open Type) for Continuously-Supported Applications



*Size .500 has oil lubricant fitting.
 Sizes .625 and above have 1/4-28
 access for lubrication.

Super Ball Bushing™ Pillow Blocks (Open Type, seal at both ends)
 (Dimensions in inches)

Catalog Number	Nominal Diameter	A	A1	A2	B	E ± .010	E1 ± .010	E2 Min.	F1
TSPB-8-OPN	.500	2.00	.69	.75	1.50	1.000	1.688	.31	.25
TSPB-10-OPN	.625	2.50	.88	.94	1.75	1.125	2.125	.37	.28
TSPB-12-OPN	.750	2.75	.94	1.00	1.88	1.250	2.375	.43	.31
TSPB-16-OPN	1.000	3.25	1.19	1.25	2.63	1.750	2.875	.56	.38
TSPB-20-OPN	1.250	4.00	1.50	1.63	3.38	2.000	3.500	.62	.44
TSPB-24-OPN	1.500	4.75	1.75	1.88	3.75	2.500	4.125	.75	.50
TSPB-32-OPN	2.000	6.00	2.25	2.44	4.75	3.250	5.250	1.00	.63

Catalog Number	G	G1	H ± .003	H1	N		Pillow Block Mass lb	Dynamic ^A Load Capacity lbf
					Hole	Bolt		
TSPB-8-OPN	.69	.75	.687	1.13	.16	#6	.2	230
TSPB-10-OPN	.42	.53	.875	1.44	.19	#8	.4	320
TSPB-12-OPN	1.08	.55	.937	1.56	.19	#8	.5	470
TSPB-16-OPN	1.37	.76	1.187	2.00	.22	#10	1.0	780
TSPB-20-OPN	1.73	1.05	1.500	2.56	.22	#10	2.1	1170
TSPB-24-OPN	2.03	1.12	1.750	2.94	.28	.25	3.2	1560
TSPB-32-OPN	2.50	1.44	2.125	3.63	.41	.38	6.0	2350

^A See the chart on the bottom half of the next page.

Continued on the next page

NOTE: Catalog number is for a standard item.
 For other options, add: **CR** Corrosion-Resistant or **NB** Nylon Balls
 to end of catalog number.