


Super Ball Bushing™ Twin Pillow Blocks (Closed Type) for End-Supported Applications



^ASizes .250, .375 and .500 have oil lubricant fitting.
Sizes .625 and above have 1/4-28 access for lubrication.

Super Ball Bushing Twin Pillow Blocks (Closed Type, seal at both ends) (Dimensions in inches)								
Catalog Number	Nominal Diameter	A	A2	B	E ± .010	E1 ± .010	F	F1
TTWN-4	.250	1.63	1.00	2.50	2.000	1.313	.75	.19
TTWN-6	.375	1.75	1.13	2.75	2.250	1.438	.88	.19
TTWN-8	.500	2.00	1.38	3.50	2.500	1.688	1.13	.25
TTWN-10	.625	2.50	1.75	4.00	3.000	2.125	1.44	.28
TTWN-12	.750	2.75	1.88	4.50	3.500	2.375	1.56	.31
TTWN-16	1.000	3.25	2.38	6.00	4.500	2.875	1.94	.38
TTWN-20	1.250	4.00	3.00	7.50	5.500	3.500	2.50	.44
TTWN-24	1.500	4.75	3.50	9.00	6.500	4.125	2.88	.50

Catalog Number	G	G1	H ± .003	H1	N		Pillow Block Mass lb	Dynamic* Load Capacity lbf
					Hole	Bolt		
TTWN-4	.44	1.25	.437	.81	.16	#6	.19	120
TTWN-6	.50	1.37	.500	.94	.16	#6	.25	200
TTWN-8	.59	1.75	.687	1.25	.16	#6	.40	510
TTWN-10	.85	2.00	.875	1.63	.19	#8	1.00	900
TTWN-12	.94	2.25	.937	1.75	.19	#8	1.20	1200
TTWN-16	1.19	3.00	1.187	2.19	.22	#10	2.40	2100
TTWN-20	1.50	3.75	1.500	2.81	.22	#10	5.00	3000
TTWN-24	1.75	4.50	1.750	3.25	.28	1/4	7.80	4000

*See the chart on the bottom half of the next page.

Continued on the next page

NOTE: Catalog number is for a standard item.
For other options, add: **CR** Corrosion-Resistant or **NB** Nylon Balls to end of catalog number.