

AGMA 10
3/16 BORE
PRECISION MATCHED SETS
20° PRESSURE ANGLE



PHONE: 516.328.3300 • FAX: 516.326.8827 • WWW.SDP-SI.COM

> MATERIAL:

303 Stainless Steel
2024-T4 or -T351 Aluminum Alloy,
anodized before cutting.

Available on special order:
Different bore size and/or material,
passivation for Stainless Steel.

Sold as Set



INCH COMPONENT

Catalog Number	Ratio	No. of Teeth	P.D.	A	Material
S1354Z-64S32A032	1:1	32	.500	.593	Stainless Steel Aluminum
S1354Z-64S32S032	1:1	32	.500	.593	Stainless Steel
S1354Z-64A32A032	1:1	32	.500	.593	Aluminum
S1354Z-64S32A048	1:1-1/2	32 48	.500 .750	.687	Stainless Steel Aluminum
S1354Z-64S32S048	1:1-1/2	32 48	.500 .750	.687	Stainless Steel
S1354Z-64A32A048	1:1-1/2	32 48	.500 .750	.687	Aluminum
S1354Z-64S32A064	1:2	32 64	.500 1.000	.781	Stainless Steel Aluminum
S1354Z-64S32S064	1:2	32 64	.500 1.000	.781	Stainless Steel
S1354Z-64A32A064	1:2	32 64	.500 1.000	.781	Aluminum
S1354Z-64S32A096	1:3	32 96	.500 1.500	1.031	Stainless Steel Aluminum
S1354Z-64S32S096	1:3	32 96	.500 1.500	1.031	Stainless Steel
S1354Z-64A32A096	1:3	32 96	.500 1.500	1.031	Aluminum
S1354Z-64S32A128	1:4	32 128	.500 2.000	1.281	Stainless Steel Aluminum
S1354Z-64S32S128	1:4	32 128	.500 2.000	1.281	Stainless Steel
S1354Z-64A32A128	1:4	32 128	.500 2.000	1.281	Aluminum